

**Flow drill - flat (no collar) Inox, Threads: M8****Order data**

Order number	080754 M8
GTIN	4069515008792
Item class	BAW

Description**Version:**

Very quickly produce core holes in thin-walled materials using frictional heat. Can be used on CNC, NC and pillar drilling machines.

Standard or long; with or without a collar.

Flow drill - flat (no collar), for use in stainless materials.

Application:

Particularly suitable for stainless steels.

Suitable for:

HOLEX ER collets No. 308964.

ER chuck key No. 309680.

HOLEX fluteless tap No. 139130 or No. 139180.

Technical description

recommended drive power	1.5 kW
Tapping hole Ø	7.4 mm
recommended speed	2300 min ⁻¹

Data sheet

Material thickness	0.7 - 1 mm
Shank Ø	8 mm
for thread M	M8
Type of product	Flow drill