

 KOMET

**KOMET Reamax® TS holder DAH® Zero Plain shank, short, for reaming head Ø D: 27-34,99mm**

**Order data**

Order number	239930 27-34,99
GTIN	
Item class	27E

**Description**
**Version:**

The holder is pre-loaded and set to < 0.005 mm run-out. For run-out accuracies to precision < 3 µm, longer tool life, and higher process reliability.

**Suitable for:**

Reaming heads No. 239805; 239811; 239816; 239822; 239826.

**Supplied with:**

Holder complete with pull stud, spanner for pull stud and activation key.  
Please order a hexagon key L-wrench separately if required.

**Technical description**

Wrench No. 239901	8AF
for reaming head Ø D	27 - 34.99 mm
Overhang A	120 mm
Overall length L <sub>tot</sub>	176 mm
Activation wrench No. 239902	3AF (5Nm)
Shank length L <sub>s</sub>	56 mm
Pull stud No. 239900	4
Shank Ø D <sub>s</sub> h6	25 mm
Shank type	short
Through-coolant	yes

Type of product

Phillips bit

---

**Accessories**

Pull stud Type 4

239900 4

Wrench for pull studs Drive SW8

239901 SW8