



KOMET Reamax® TS holder Plain shank, long, for reaming head Ø D: 27-34,99mm



Order data

Order number	239890 27-34,99
GTIN	4047109280137
Item class	27E

Description

Suitable for :

Reaming heads No. 239805; 239811; 239816; 239822; 239826.

Supplied with:

Holder complete with pull stud, spanner for pull stud and activation key.

Please order a hexagon key L-wrench separately if required.

Through-coolant: yes

Overhang A: 180 mm

Overall length L_{tot} : 236 mm

Shank length L_s : 56 mm

Shank Ø D_s h6: 25 mm

Pull stud No. 239900: 4

Wrench No. 239901: 8AF

Technical description

Overhang A	180 mm
Pull stud No. 239900	4
Activation wrench No. 239902	3AF (5Nm)
Overall length L_{tot}	236 mm
Wrench No. 239901	8AF
Shank length L_s	56 mm
for reaming head Ø D	27 - 34.99 mm
Shank Ø D_s h6	25 mm

Shank type	long
Through-coolant	yes
Type of product	Phillips bit

Accessories

Wrench for pull studs Drive SW8	239901 SW8
Pull stud Type 4	239900 4