

**Garant****GARANT Uni Hero solid carbide drill plain shank DIN 6535 HA, TiAlSiN, Ø DC h7: 12,5mm****Order data**

|              |               |
|--------------|---------------|
| Order number | 122450 12,5   |
| GTIN         | 4069515009904 |
| Item class   | 13M           |

**Description****Version:**

**The ultimate in universality and profitability** in one tool. **Robust tool design** and **convex-concave curved cutting edge design** for optimum tool stability and chip breakage behaviour in a wide range of materials. **Special flute geometry** and **polished flutes** for ideal chip evacuation and maximum process reliability. **Ultra-smooth TiAlSiN high-performance coating** to effectively reduce wear and the formation of built-up edges.

**Note:**

Flute length  $L_c = L_2 + 1.5 \times D_c$ .

HB and HE shanks are available at the same price as HA.

For **HB shanks**: use order **no. 122451**.

For **HE shanks**: order with **No. 122450** and **12900HE**.

Articles with prices in brackets: Different delivery time and minimum order quantity is 3 pieces.

**Technical description**

|                                          |              |
|------------------------------------------|--------------|
| Nominal Ø D <sub>c</sub>                 | 12.5 mm      |
| Number of cutting edges Z                | 2            |
| Standard                                 | DIN 6537 K   |
| Feed f in steel < 1100 N/mm <sup>2</sup> | 0.25 mm/rev. |
| Flute length L <sub>c</sub>              | 60 mm        |
| Shank Ø D <sub>s</sub>                   | 14 mm        |
| Overall length L                         | 107 mm       |

## Data sheet

|                                          |                   |
|------------------------------------------|-------------------|
| recommended maximum drilling depth $L_2$ | 41.3 mm           |
| Tolerance nominal $\varnothing$          | h7                |
| Series                                   | Uni               |
| Coating                                  | TiAlSiN           |
| Tool material                            | Solid carbide     |
| Version                                  | 4xD               |
| Point angle                              | 140 degrees       |
| Shank                                    | DIN 6535 HA to h6 |
| Through-coolant                          | yes, with 25 bar  |
| Machining strategy                       | HPC               |
| Semi-Standard                            | yes               |
| Colour ring                              | orange            |
| Type of product                          | Jobber drill      |

## User data

|                                | Suitability                               | $V_c$     | ISO code |
|--------------------------------|-------------------------------------------|-----------|----------|
| Alu plastics                   | suitable only under restricted conditions | 190 m/min | N        |
| Aluminium (short chipping)     | suitable                                  | 200 m/min | N        |
| Steel < 500 N/mm <sup>2</sup>  | suitable                                  | 160 m/min | P        |
| Steel < 750 N/mm <sup>2</sup>  | suitable                                  | 150 m/min | P        |
| Steel < 900 N/mm <sup>2</sup>  | suitable                                  | 140 m/min | P        |
| Steel < 1100 N/mm <sup>2</sup> | suitable                                  | 110 m/min | P        |
| Steel < 1400 N/mm <sup>2</sup> | suitable                                  | 90 m/min  | P        |
| INOX < 900 N/mm <sup>2</sup>   | suitable                                  | 90 m/min  | M        |
| INOX > 900 N/mm <sup>2</sup>   | suitable                                  | 80 m/min  | M        |
| Ti > 850 N/mm <sup>2</sup>     | suitable                                  | 40 m/min  | S        |
| GG(G)                          | suitable                                  | 130 m/min | K        |

|             |                                              |
|-------------|----------------------------------------------|
| Uni         | suitable                                     |
| wet maximum | suitable                                     |
| wet minimum | suitable                                     |
| Air         | suitable only under<br>restricted conditions |

**Suitable products**

<https://www.hoffmann-group.com/GB/en/hom/p/122450-12,5>