

 KOMET

KOMET Reamax® TS holder DAH® Zero Plain shank, short, for reaming head Ø D: 35-41,99mm

Order data

Order number	239930 35-41,99
GTIN	
Item class	27E

Description
Version:

The holder is pre-loaded and set to < 0.005 mm run-out. For run-out accuracies to precision < 3 µm, longer tool life, and higher process reliability.

Suitable for:

Reaming heads No. 239805; 239811; 239816; 239822; 239826.

Supplied with:

Holder complete with pull stud, spanner for pull stud and activation key.
Please order a hexagon key L-wrench separately if required.

Technical description

Shank length L_s	56 mm
for reaming head Ø D	35 - 41.99 mm
Wrench No. 239901	10AF
Overall length L_{tot}	176 mm
Activation wrench No. 239902	3AF (6Nm)
Pull stud No. 239900	5
Overhang A	120 mm
Shank Ø D_s h6	25 mm
Shank type	short
Through-coolant	yes

Type of product

Phillips bit

Accessories

Pull stud Type 5

239900 5

Wrench for pull studs Drive SW10

239901 SW10