

 KOMET

**KOMET Reamax® TS holder Plain shank, short, for reaming head Ø D:
20-21,99mm**

Order data

Order number	239880 20-21,99
GTIN	4047109229327
Item class	27E

Description
Suitable for :

Reaming heads No. 239805; 239811; 239816; 239822; 239826.

Supplied with:

Holder complete with pull stud, spanner for pull stud and activation key.

Please order a hexagon key L-wrench separately if required.

Through-coolant: yes

Overhang A: 80 mm

Overall length L_{tot} : 130 mm

Shank length L_s : 50 mm

Shank Ø D_s h6: 20 mm

Pull stud No. 239900: 2

Wrench No. 239901: 5AF

Technical description

Overall length L_{tot}	130 mm
Activation wrench No. 239902	2.5AF (2.5Nm)
Pull stud No. 239900	2
for reaming head Ø D	20 - 21.99 mm
Overhang A	80 mm
Wrench No. 239901	5AF
Shank length L_s	50 mm

Shank \varnothing D _s h6	20 mm
Shank type	short
Through-coolant	yes
Type of product	Phillips bit

Accessories

Pull stud Type 2	239900 2
Wrench for pull studs Drive SW5	239901 SW5