

 KOMET

KOMET Reamax® TS holder DAH® Zero Plain shank, long, for reaming head Ø D: 20-21,99mm

Order data

Order number	239940 20-21,99
GTIN	
Item class	27E

Description
Version:

The holder is pre-loaded and set to < 0.005 mm run-out. For run-out accuracies to precision < 3 µm, longer tool life, and higher process reliability.

Suitable for:

Reaming heads No. 239805; 239811; 239816; 239822; 239826.

Supplied with:

Holder complete with pull stud, spanner for pull stud and activation key.
Please order a hexagon key L-wrench separately if required.

Technical description

for reaming head Ø D	20 - 21.99 mm
Wrench No. 239901	5AF
Pull stud No. 239900	2
Shank length L _s	50 mm
Overhang A	140 mm
Overall length L _{tot}	205 mm
Activation wrench No. 239902	2.5AF (2.5Nm)
Shank Ø D _s h6	20 mm
Shank type	long
Through-coolant	yes
Type of product	Phillips bit

Accessories

Pull stud Type 2

239900 2

Wrench for pull studs Drive SW5

239901 SW5