

Garant**Modular NC high-pressure vice LCV 125 G, Jaw width A: 125GSTmm****Order data**

Order number	361290 125GST
GTIN	4069515011259
Item class	31H

Description**Version:**

Top and bottom faces ground. **With 25H6 M10 holes at 200 mm pitch for zero-point clamping system.**

Feature: Sturdy, compact base body (GGG 60) with large capacity. Fully enclosed and nitrided spindle (increased operational reliability, optimised swarf protection, minimised cleaning requirement).

Function:

Clamping with adjustable torque wrench (maximum 30 Nm) with special high pressure spindle and mechanical power intensifier up to 2.5 mm.

Application:

Due to the 2.5 mm power stroke of the spindle, suitable for conventional clamping using stepped jaws and Gripp jaws.

Supplied with:

Including stepped jaws (No. 361400 125; 361348 125), 4 pcs. gripper inserts (No. 361160 7); 4 pcs. gripper inserts (No. 361240 1) and clamping claws (No. 360750 125/160).

Optional extras:

Jaws (see No. 361331–361970), torque wrench No. 656050 size 60, clamping stud No. 360025.

Technical description

Colour code for suitable accessories	LCV125G
Torque	30 Nm

Data sheet

Clamping force up to maximum	40 kN
Weight	33 kg
Version	Zero-point clamping system
maximum clamping range	331 mm
Type of product	Machine vice

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/361290-125GST>