



## KOMET® roughing bar Form g, Type: B03



### Order data

Order number	240074 B03
GTIN	4047109016491
Item class	24H

### Description

#### Version:

Microscopically tested, precise cutting profile. Cost-efficient due to multiple regrinding of the cutting face.

Sizes with suffix **L** = **extended shank**.

#### Tool material:

**HSS/Co10** – for difficult to machine materials.

#### Note:

**For suitable boring bar holders see No. 240070 and No. 240072.**

Tool material: HSS Co 10

Boring depth: 26 mm

for bores from Ø: 7 mm

Overall length: 65 mm

Shank Ø: 8 mm

### Technical description

for bores from Ø	7 mm
Overall length	65 mm
Boring depth	26 mm
Type	B03
Shank Ø	8 mm
Tool material	HSS Co 10
Type of product	Cutter insert for turning

