

Garant

Eco BMT longitudinal toolholder, BMT: 65



Order data

Order number	319884 65
GTIN	4069515001427
Item class	31V

Description

Version:

For internal and external cooling.

High-precision arbors adapted to the specific machine, for flexible use on main and counter-spindle machines. Contact face and functional face ground. Perfectly matched for the respective lathe.

Suitable for efficient cooling systems such as GARANT eco, but also for other systems. Optimised outer contour. Scale to optimally adjust the machining tool. Spring-mounted pressure pad for uniform clamping of the turning tools.

Suitable for conventional toolholders.

Advantage:

- **Design optimised for weight and geometry.**
- **Process reliability thanks to high-quality materials, long working life.**
- **Burnished for better corrosion protection.**
- **With secured ball injection nozzles up to 80 bar.**

Application:

Mainly for external machining.

Internal and external machining in CNC lathes with BMT tool turrets.

Suitable for:

CNC lathes with BMT tool turret.

Note:
Other BMT holders with different sizes and dimensions are available on request.

Technical description

h ₂	97 mm
L ₁	70 mm
L ₂	73 mm
x	75 mm
h ₁	25 mm
Type of product	Steel toolholder