

Garant

Eco BMT transverse toolholder, BMT: 65



Order data

Order number	319886 65
GTIN	4069515001465
Item class	31V

Description

Version:

Suitable for efficient cooling systems such as GARANT eco, but also for other systems. Optimised outer contour. Scale to optimally adjust the machining tool. Spring-mounted pressure pad for uniform clamping of the turning tools.

For internal and external cooling.

High-precision arbors adapted to the specific machine, for flexible use on main and counter-spindle machines. Contact face and functional face ground. Perfectly matched for the respective lathe.

Suitable for conventional toolholders.

Advantage:

- **Design optimised for weight and geometry.**
- **Process reliability thanks to high-quality materials, long working life.**
- **Burnished for better corrosion protection.**
- **With secured ball injection nozzles up to 80 bar.**

Application:

Internal and external machining in CNC lathes with BMT tool turrets.

Primarily for facing and internal machining.

Suitable for:

CNC lathes with BMT tool turret.

Note:

Other BMT holders with different sizes and dimensions are available on request.

Technical description

h_2	85 mm
x	60 mm
Suitable machines	Doosan Lynx, Doosan Puma, Hwacheon
b_2	70.5 mm
L_1	70 mm
L_2	73 mm
h_1	25 mm
Type of product	Steel toolholder