

 KOMET

KOMET® internal thread boring bar, right-hand Form 55°(Whitworth), Type: B06

Order data

Order number	240088 B06
GTIN	4047109017177
Item class	24H

Description
Version:

Microscopically tested, precise cutting profile. Cost-efficient due to multiple regrinding of the cutting face.

Sizes with suffix **L = extended shank.**

Tool material:

HSS/Co10 – for difficult to machine materials.

Note:

For suitable boring bar holders see No. 240070 and No. 240072.

Technical description

for pitches	8–30 threads/inch
Overall length	95 mm
for bores from Ø	14 mm
Boring depth	60 mm
Type	B06
Shank Ø	10 mm
Tool material	HSS Co 10
Type of product	Cutter insert for turning

