


**KOMET® UniTurn® copying boring bar, right-hand, L<sub>2</sub> = 35 mm, Ø D<sub>min</sub>: 6mm**

**Order data**

Order number	240130 6
GTIN	4047109071315
Item class	24S

**Description**
**Version:**

Tool material = BK 82.

From size 5 with internal coolant supply; for smaller diameters, the coolant supply takes place through the toolholder.

**Technical description**

max. groove depth $t_{\max}$	1.8 mm
for bores from $\varnothing D_{\min}$	6 mm
Shank $\varnothing d$	8 mm
a	5.7 mm
Suitable toolholder No. 240100	12/8; 16/8
f	2.75 mm
Radius R	0.2 mm
maximum cutting depth $a_{p\max}$	0.5 mm
Through-coolant	yes
Feed f in steel < 500 N/mm <sup>2</sup>	0.02 mm/rev.
Usable length	35 mm
Product name attribute	L <sub>2</sub> = 35 mm
Type of product	Cutter insert for turning

## User data

	Suitability	V <sub>c</sub>	ISO code
Alu plastics	suitable	180 m/min	N
Aluminium (short chipping)	suitable	180 m/min	N
Alu > 10% Si	suitable	160 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable	100 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	90 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	80 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	70 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable	70 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable	50 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable	50 m/min	M
Ti > 850 N/mm <sup>2</sup>	suitable	30 m/min	S
GG(G)	suitable	55 m/min	K
Uni	suitable		
wet maximum	suitable		
dry	suitable only under restricted conditions		

## Accessories

KOMET UniTurn® turning toolholder for stationary use  
(without boring bar) Shank Ø d / Bore Ø d1 12/8 mm

240100 12/8

KOMET UniTurn® turning toolholder for stationary use  
(without boring bar) Shank Ø d / Bore Ø d1 16/8 mm

240100 16/8