


 KOMET

**KOMET UniTurn® turning toolholder for stationary use (without boring bar),  
Shank  $\varnothing$  d / Bore  $\varnothing$  d1: 16/4mm**

**Order data**

Order number	240100 16/4
GTIN	4047109019355
Item class	24S

**Description**
**Application:**

For turning and internal grooving on the lathe.

**Technical description**

Length a	10 mm
Shank $\varnothing$ d	16 mm
Clamping height b	15 mm
Overall length $L_{tot}$	70 mm
Length $l_2$	50 mm
Bore $\varnothing$ d <sub>1</sub>	4 mm
Through-coolant	yes
Type of product	Cutter holder