

Garant
Boring bar carbide, left-hand, Shank \varnothing / insert size: 20/09mm

Order data

Order number	260017 20/09
GTIN	4045197651921
Item class	21T

Technical description

Head length L_1	16 mm
Pack of insert screws	269028 8
Insert size	9 mm
suitable indexable insert	CC.. 09T3..
ISO code toolholder	E20S SCLCR/L09
Centre offset L_3	12 mm
Minimum pre-drill $\varnothing D_{\min}$	23 mm
Overall length L	250 mm
Clamping height L_2	19 mm
Setting angle κ	95 degrees
Shank $\varnothing D_s$	20 mm
Standard	DIN 8024
Application type	left-hand
Boring depth up to	8xD
Tool material	Carbide
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15

674248 TX15

Set of insert screws Type 8

269028 8

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm

659957 500