

Garant
QuickTurn clamp toolholder, right-hand, Shank / insert size: 20/11mm

Order data

| | |
|--------------|---------------|
| Order number | 250606 20/11 |
| GTIN | 4045197650368 |
| Item class | 21U |

Description
Advantage:

Inserts can be changed without using tools. **Release the stop at the push of a button – change the insert – press the clamp to secure it.**

A simple and convenient way to reduce non-productive times.

Consistent clamping force, high interchange accuracy, maintenance-free.

Through-coolant: no

ISO code toolholder: DDJNR/L 2025K11

suitable indexable insert: DN.. 1104..

Functional width L_4 : 32 mm

Head length L_1 : 48.5 mm

Overall length L: 125 mm

Shim: 259031 8

Technical description

| | |
|---------------------------|-----------------|
| Shim | 259031 8 |
| ISO code toolholder | DDJNR/L 2025K11 |
| suitable indexable insert | DN.. 1104.. |
| Head length L_1 | 48.5 mm |
| Insert size | 11 mm |
| Clamp | 259038 6 |
| Shim screw | 259025 5 |

| | |
|---------------------------------|-------------------------------|
| Functional width L ₄ | 32 mm |
| Shank size | 20 mm |
| Overall length L | 125 mm |
| Series | QuickTurn |
| Application type | right-hand |
| Standard | DIN ISO 5610 |
| Through-coolant | no |
| Setting angle κ | 93 ° |
| Application | External longitudinal turning |
| Application | External longitudinal turning |
| Type of product | Boring bar |

Accessories

| | |
|--|------------|
| Shim | 259211 |
| Clamping claw | 259350 |
| Shim Type 8 | 259031 8 |
| PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8 | 674248 TX8 |
| Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm | 659906 500 |
| Shim screw | 259174 |
| Shim screw Type 5 | 259025 5 |
| Clamping claw Type 6 | 259038 6 |