

Garant
QuickTurn clamping toolholder DDJNR 93°, for indexable inserts DN., right-hand

Order data

Order number	250606 25/11
GTIN	4045197650375
Item class	21U

Description
Advantage:

Inserts can be changed without using tools. **Release the stop at the push of a button – change the insert – press the clamp to secure it.**

A simple and convenient way to reduce non-productive times.

Consistent clamping force, high interchange accuracy, maintenance-free.

Technical description

suitable indexable insert	DN.. 1104..
Functional width L ₄	32 mm
ISO code toolholder	DDJNR/L 2525M11
Shim	259031 8
Head length L ₁	48.5 mm
Shank size	25 mm
Insert size	11 mm
Clamp	259038 6
Shim screw	259025 5
Overall length L	150 mm
Series	QuickTurn

Application type	right-hand
Through-coolant	no
Setting angle κ	93 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Shim screw Type 5	259025 5
Shim Type 8	259031 8
Clamping claw Type 6	259038 6
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8