

Garant
QuickTurn clamp toolholder, right-hand, Shank / insert size: 20/15mm

Order data

Order number	250606 20/15
GTIN	4045197650382
Item class	21U

Description
Advantage:

Inserts can be changed without using tools. **Release the stop at the push of a button – change the insert – press the clamp to secure it.**

A simple and convenient way to reduce non-productive times.

Consistent clamping force, high interchange accuracy, maintenance-free.

Through-coolant: no

ISO code toolholder: DDJNR/L 2025K15

suitable indexable insert: DN.. 1506..

Functional width L_4 : 32 mm

Head length L_1 : 46 mm

Overall length L: 125 mm

Shim: 259031 29

Technical description

suitable indexable insert	DN.. 1506..
Shim screw	259025 4
Head length L_1	46 mm
Clamp	259038 7
Shank size	20 mm
Functional width L_4	32 mm
ISO code toolholder	DDJNR/L 2025K15

Shim	259031 29
Insert size	15 mm
Overall length L	125 mm
Series	QuickTurn
Application type	right-hand
Standard	DIN ISO 5610
Through-coolant	no
Setting angle κ	93 °
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Clamping claw	259351
Shim screw Type 4	259025 4
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659906 500
Shim	259271
Shim Type 29	259031 29
Clamping claw	259350
Shim screw	259171
Clamping claw Type 6	259038 6
Clamping claw Type 7	259038 7