



## KOMET KUB Trigon® indexable drill Combination shank, 3×D, Ø DC: 19mm



### Order data

Order number	236630 19
GTIN	4047109100176
Item class	24P

### Description

#### Version:

- **Offset-axis drilling: dependent on Ø up to 1.5 mm.**
- **Special manufacturing procedure for extremely large flutes with very high rigidity.**
- **Specific positioning of the indexable inserts for bores free of withdrawal marks and with precise dimensional stability ( $\pm 0.1$  mm as a rule).**
- **Internal coolant supply is directed to the cutting edges (sophisticated geometry, ideal for minimum lubrication).**
- **3 – 10 bar coolant pressure is sufficient.**
- **For stationary and rotating applications.**

#### Application:

With indexable inserts No. 236740 – 237080.

#### Supplied with:

Clamp screws (without indexable inserts).

#### Note:

- **Note! A disc falls off when the drill exits. Risk of injury if the component is rotating! Please take safety precautions.**
- **On request – left-hand cutting; – 2×D, – other Ø; – special types – torsional vibration damper for ABS giving low-vibration machining, with maximum tool life and minimum noise level.**

### Technical description

ISO code indexable insert	WOEX 030204 10-...
Shank Ø D <sub>s</sub>	25 mm
Pack of insert screws	239652 6IP1 (0.6 Nm)
achievable maximum Ø offset	20 mm

Number of cutting edges Z	1
Reach L <sub>1</sub>	57 mm
Shank length L <sub>s</sub>	56 mm
Series	KUB Trigon®
Nominal Ø D	19
for inch Ø	3/4 in
Maximum adjustment limit V <sub>max</sub>	0.5 mm
Overhang L <sub>A</sub>	81 mm
Drill depth for indexable insert drill up to	3×D
Shank	DIN 6535 HE, DIN 6595
Use for drilling	Centre drilling
Use for drilling	limited cross-drilling
Use for drilling	oblique spot drilling
Use for drilling	limited cross-drilling
Use for drilling	Aperture
Use for drilling	oblique exit
Use for drilling	convex
Through-coolant	yes
Type of product	Indexable drill

## Accessories

Torx Plus® insert screw set 10 pieces Drive 6IP1	239652 6IP1
Torque screwdriver, fixed setting set torque 0,6 N·m	211750 0,6
PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 6IP	674252 6IP