

Garant
QuickTurn clamp toolholder, left-hand, Shank / insert size: 20/11 mm

Order data

Order number	250607 20/11
GTIN	4045197650405
Item class	21U

Description
Advantage:

Inserts can be changed without using tools. **Release the stop at the push of a button – change the insert – press the clamp to secure it.**

A simple and convenient way to reduce non-productive times.

Consistent clamping force, high interchange accuracy, maintenance-free.

Through-coolant: no

ISO code toolholder: DDJNR/L 2025K11

suitable indexable insert: DN.. 1104..

Functional width L_4 : 32 mm

Head length L_1 : 48.5 mm

Overall length L: 125 mm

Shim: 259031 8

Technical description

suitable indexable insert	DN.. 1104..
Shank size	20 mm
Insert size	11 mm
Clamp	259038 6
Functional width L_4	32 mm
ISO code toolholder	DDJNR/L 2025K11
Head length L_1	48.5 mm

Shim screw	259025 5
Shim	259031 8
Overall length L	125 mm
Series	QuickTurn
Application type	left-hand
Standard	DIN ISO 5610
Through-coolant	no
Setting angle κ	93 °
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8
Shim	259211
Shim screw	259174
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659906 500
Shim screw Type 5	259025 5
Clamping claw Type 6	259038 6
Shim Type 8	259031 8
Clamping claw	259350