

Garant
QuickTurn clamp toolholder, left-hand, Shank / insert size: 25/11mm

Order data

Order number	250607 25/11
GTIN	4045197650412
Item class	21U

Description
Advantage:

Inserts can be changed without using tools. **Release the stop at the push of a button – change the insert – press the clamp to secure it.**

A simple and convenient way to reduce non-productive times.

Consistent clamping force, high interchange accuracy, maintenance-free.

Through-coolant: no

ISO code toolholder: DDJNR/L 2525M11

suitable indexable insert: DN.. 1104..

Functional width L₄: 32 mm

Head length L₁: 48.5 mm

Overall length L: 150 mm

Shim: 259031 8

Technical description

Insert size	11 mm
Functional width L ₄	32 mm
Head length L ₁	48.5 mm
Shim	259031 8
Shank size	25 mm
suitable indexable insert	DN.. 1104..
Clamp	259038 6

ISO code toolholder	DDJNR/L 2525M11
Shim screw	259025 5
Overall length L	150 mm
Series	QuickTurn
Application type	left-hand
Standard	DIN ISO 5610
Through-coolant	no
Setting angle κ	93 °
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Clamping claw	259350
Shim Type 8	259031 8
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659906 500
Shim screw Type 5	259025 5
Shim screw	259174
Clamping claw Type 6	259038 6
Shim	259211