

Garant**Indexable insert for turning CNMM 160612, for coarse machining****Order data**

Order number	250458 HB7130-2
GTIN	4069515023023
Item class	21G

Technical description

Tool material	Carbide
Type	HB7130-2
Cutting conditions	slightly interrupted
Feed f	0.2 - 0.9 mm/rev.
Main application	M
Number of changes/inserts	4
Corner radius	1.2 mm
Cutting depth a_p	2 - 10 mm
ISO code indexable insert	CNMM 160612
Finishing/roughing assignment	Roughing
Cutting speed v_c main application	50 - 200 m/min

Chip breaker	VR
Type of product	Indexable insert for turning