

Garant**Indexable insert for turning CNMG 120416, for roughing machining****Order data**

Order number	250328 HB7010-2
GTIN	4069515016285
Item class	21G

Technical description

Main application	P
Type	HB7010-2
Cutting speed v_c main application	120 - 415 m/min
Corner radius	1.6 mm
Number of changes/inserts	4
ISO code indexable insert	CNMG 120416
Cutting depth a_p	1.5 - 6 mm
Feed f	0.25 - 0.6 mm/rev.
Finishing/roughing assignment	Roughing
Cutting conditions	continuous
Tool material	Carbide

Chip breaker	SG
Type of product	Indexable insert for turning