

Garant**Indexable insert for turning DNMG 150612, for medium machining****Order data**

Order number	250764 HB7010-2
GTIN	4069515022972
Item class	21G

Technical description

Type	HB7010-2
Number of changes/inserts	4
Main application	P
ISO code indexable insert	DNMG 150612
Cutting conditions	continuous
Cutting depth a_p	0.3 - 4 mm
Feed f	0.2 - 0.5 mm/rev.
Finishing/roughing assignment	Finishing
Chip breaker	SM
Tolerance	M
Corner radius	1.2 mm

Data sheet

Cutting speed v_c main application	140 - 440 m/min
Tool material	Carbide
Type of product	Indexable insert for turning