

**Indexable insert for turning SNMG 150612, for roughing machining****Order data**

Order number	251330 HB7020-2
GTIN	4069515022996
Item class	21G

Technical description

Type	HB7020-2
Cutting speed v_c main application	110 - 360 m/min
ISO code indexable insert	SNMG 150612
Main application	P
Feed f	0.25 - 0.6 mm/rev.
Number of changes/inserts	8
Tool material	Carbide
Cutting depth a_p	1.5 - 6 mm
Finishing/roughing assignment	Roughing
Cutting conditions	slightly interrupted
Corner radius	1.2 mm

Data sheet

Chip breaker	SG
Type of product	Indexable insert for turning