


Garant**Indexable insert for turning SNMG 150612, for roughing machining****Order data**

Order number	251330 HB7130-2
GTIN	4069515023054
Item class	21G

Technical description

Type	HB7130-2
Cutting depth a_p	1.5 - 7 mm
Cutting speed v_c main application	60 - 220 m/min
Tool material	Carbide
Chip breaker	VG
Finishing/roughing assignment	Roughing
Corner radius	1.2 mm
Main application	M
Number of changes/inserts	8
ISO code indexable insert	SNMG 150612
Feed f	0.2 - 0.55 mm/rev.

Data sheet

Cutting conditions

slightly interrupted

Type of product

Indexable insert for turning