

Garant**Indexable insert for turning DNMG 150608, for finish machining****Order data**

Order number	250660 HB7010-2
GTIN	4069515016841
Item class	21G

Technical description

Corner radius	0.8 mm
ISO code indexable insert	DNMG 150608
Chip breaker	SS
Finishing/roughing assignment	Finishing
Cutting speed v_c main application	170 - 500 m/min
Cutting depth a_p	0.3 - 2 mm
Cutting conditions	continuous
Type	HB7010-2
Main application	P
Number of changes/inserts	4
Tool material	Carbide

Data sheet

Feed f	0.1 - 0.4 mm/rev.
Type of product	Indexable insert for turning