

Garant**Indexable insert for turning DNMG 150608, for medium machining****Order data**

Order number	250762 HB7010-2
GTIN	4069515017107
Item class	21G

Technical description

Feed f	0.2 - 0.5 mm/rev.
ISO code indexable insert	DNMG 150608
Cutting speed v_c main application	140 - 440 m/min
Corner radius	0.8 mm
Finishing/roughing assignment	Finishing
Chip breaker	SM
Type	HB7010-2
Cutting depth a_p	0.3 - 4 mm
Tolerance	M
Main application	P
Cutting conditions	continuous

Data sheet

Number of changes/inserts	4
Tool material	Carbide
Type of product	Indexable insert for turning