

Garant**Indexable insert for turning CNMM 120408, for coarse machining****Order data**

Order number	250452 HB7020-2
GTIN	4069515016520
Item class	21G

Technical description

Main application	P
Corner radius	0.8 mm
Cutting speed v_c main application	140 - 300 m/min
Tool material	Carbide
Number of changes/inserts	4
ISO code indexable insert	CNMM 120408
Feed f	0.4 - 1.2 mm/rev.
Cutting depth a_p	2 - 10 mm
Type	HB7020-2
Finishing/roughing assignment	Roughing
Cutting conditions	slightly interrupted

Chip breaker	SR
Type of product	Indexable insert for turning