

Garant**Indexable insert for turning DNMG 150608, for roughing machining****Order data**

Order number	250862 HB7010-2
GTIN	4069515017220
Item class	21G

Technical description

ISO code indexable insert	DNMG 150608
Number of changes/inserts	4
Cutting depth a_p	1.5 - 6 mm
Finishing/roughing assignment	Finishing
Chip breaker	SG
Cutting conditions	continuous
Corner radius	0.8 mm
Main application	P
Feed f	0.25 - 0.6 mm/rev.
Tool material	Carbide
Cutting speed v_c main application	120 - 415 m/min

Data sheet

Type	HB7010-2
Type of product	Indexable insert for turning