

Garant**Indexable insert for turning KNUX 160405R, for medium machining****Order data**

Order number	251030 HB7020-2
GTIN	4069515017343
Item class	21G

Technical description

Cutting depth a_p	0.3 - 4 mm
Finishing/roughing assignment	Finishing
Feed f	0.2 - 0.5 mm/rev.
Cutting conditions	slightly interrupted
Cutting speed v_c main application	130 - 370 m/min
Chip breaker	SM
Chip diverter	2.2 mm
Type	HB7020-2
Tool material	Carbide
Main application	P
Number of changes/inserts	2
ISO code indexable insert	KNUX 160405R
Type of product	Indexable insert for turning