

**Indexable insert for turning DNMG 110404, for medium machining****Order data**

Order number	250752 HB7010-2
GTIN	4069515016926
Item class	21G

Technical description

Cutting speed v_c main application	140 - 440 m/min
Number of changes/inserts	4
Feed f	0.2 - 0.5 mm/rev.
Cutting conditions	continuous
ISO code indexable insert	DNMG 110404
Main application	P
Finishing/roughing assignment	Finishing
Type	HB7010-2
Tolerance	M
Chip breaker	SM
Tool material	Carbide

Data sheet

Cutting depth a_p	0.3 - 4 mm
Corner radius	0.4 mm
Type of product	Indexable insert for turning