

Garant**Indexable insert for turning DC.T 11T304, for medium machining****Order data**

Order number	260462 HB7020-2
GTIN	4069515020640
Item class	21G

Technical description

Cutting speed v_c main application	110 - 350 m/min
Cutting depth a_p	0.3 - 2 mm
Feed f	0.08 - 0.3 mm/rev.
Tool material	Carbide
Cutting conditions	slightly interrupted
Chip breaker	SM
Corner radius	0.4 mm
Finishing/roughing assignment	Finishing
Number of changes/inserts	2
Type	HB7020-2
Tolerance	M

Data sheet

ISO code indexable insert	DCMT 11T304
Main application	P
Type of product	Indexable insert for turning