

**Indexable insert for turning DNMG 110404, for finish machining****Order data**

Order number	250652 HB7010-2
GTIN	4069515016605
Item class	21G

Technical description

Main application	P
Cutting depth a_p	0.3 - 2 mm
Number of changes/inserts	4
Finishing/roughing assignment	Finishing
Corner radius	0.4 mm
Type	HB7010-2
Cutting conditions	continuous
Feed f	0.1 - 0.4 mm/rev.
Cutting speed v_c main application	170 - 500 m/min
Tool material	Carbide
Chip breaker	SS

Data sheet

ISO code indexable insert

DNMG110404

Type of product

Indexable insert for turning