

Garant**Indexable insert for turning VB.T 160408, for medium machining****Order data**

Order number	261234 HB7020-2
GTIN	4069515022231
Item class	21G

Technical description

Corner radius	0.8 mm
Tool material	Carbide
Main application	P
ISO code indexable insert	VBMT 160408
Chip breaker	SM
Feed f	0.08 - 0.3 mm/rev.
Cutting speed v_c main application	110 - 350 m/min
Number of changes/inserts	2
Finishing/roughing assignment	Finishing
Cutting conditions	slightly interrupted
Cutting depth a_p	0.3 - 2 mm

Data sheet

Type	HB7020-2
Tolerance	M
Type of product	Indexable insert for turning