

Garant**Indexable insert for turning VBMT 160402, for finish machining****Order data**

Order number	261150 HB7010-2
GTIN	4069515021913
Item class	21G

Technical description

Type	HB7010-2
Cutting depth a_p	0.2 - 1.5 mm
Chip breaker	SS
Main application	P
Cutting conditions	continuous
Tool material	Carbide
Number of changes/inserts	2
Corner radius	0.2 mm
ISO code indexable insert	VBMT 160402
Feed f	0.07 - 0.25 mm/rev.
Finishing/roughing assignment	Finishing

Data sheet

Cutting speed v_c main application

150 - 500 m/min

Type of product

Indexable insert for turning