

Garant**GARANT Vap Tap machine tap left-hand thread HSS-E 6H, vaporised, M-LH: M5****Order data**

Order number	132802 M5
GTIN	4069515001922
Item class	13V

Description**Version:**

GARANT Vap Tap universal tap – left-hand thread can be used reliably in a **wide range of materials**. Optimised **neck and flute length** for **improved chip evacuation** when working on **deep** threads. High-performance **HSS-E tool material** with higher vanadium content for improved **wear resistance**. **Surface vaporised** for reduced edge build-up.

Technical description

Thread type	M-LH
Thread Ø	5 mm
Overall length L	70 mm
Number of cutting edges Z	3
Tolerance class	ISO 2 6H
Tapping hole Ø	4.2 mm
Tool material	HSS E
Number of clamping slots	3
Thread size	M5
Standard	DIN 371
Shank Ø D _s	6 mm
Shank square □	4.9 mm

Data sheet

Thread pitch	0.8 mm
Thread depth	15 mm
Coating	vaporised
Flank angle	60 degrees
Thread standard	DIN 13
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	left-hand
Type of threading tool	Machine tap for dynamic machining
Colour ring	green
Series	Vap Tap
Type of product	Taps

User data

	Suitability	V_c	ISO code
Alu plastics	suitable	18 m/min	N
Aluminium (short chipping)	suitable	13 m/min	N
Steel < 500 N/mm ²	suitable	18 m/min	P
Steel < 750 N/mm ²	suitable	15 m/min	P
Steel < 900 N/mm ²	suitable	15 m/min	P
Steel < 1100 N/mm ²	suitable	6 m/min	P
INOX < 900 N/mm ²	suitable	6 m/min	M
CuZn	suitable only under restricted conditions	15 m/min	N
Uni	suitable		
Oil	suitable		

wet maximum	suitable
-------------	----------