

**Indexable insert for turning WNMG 060408, for finish machining****Order data**

Order number	251954 HB7035-2
GTIN	4069515018463
Item class	21G

Technical description

Main application	P
Tool material	Carbide
Cutting speed v_c main application	150 - 350 m/min
Cutting depth a_p	0.3 - 2 mm
Corner radius	0.8 mm
Finishing/roughing assignment	Finishing
ISO code indexable insert	WNMG 060408
Feed f	0.1 - 0.4 mm/rev.
Number of changes/inserts	6
Cutting conditions	heavily interrupted
Chip breaker	SS
Type	HB7035-2

Type of product

Indexable insert for turning