

Garant**Indexable insert for turning DNMG 110408, for medium machining****Order data**

Order number	250754 HB7010-2
GTIN	4069515016988
Item class	21G

Technical description

Cutting depth a_p	0.3 - 4 mm
Tool material	Carbide
Tolerance	M
Chip breaker	SM
Corner radius	0.8 mm
Finishing/roughing assignment	Finishing
Cutting conditions	continuous
Number of changes/inserts	4
Main application	P
Type	HB7010-2
Cutting speed v_c main application	140 - 440 m/min

Data sheet

Feed f	0.2 - 0.5 mm/rev.
ISO code indexable insert	DNMG 110408
Type of product	Indexable insert for turning