

Garant**Indexable insert for turning VC.T 160402, for finish machining****Order data**

Order number	261370 HB7020-2
GTIN	4069515022415
Item class	21G

Technical description

Tool material	Carbide
Type	HB7020-2
Feed f	0.07 - 0.25 mm/rev.
Tolerance	M
Finishing/roughing assignment	Finishing
Cutting depth a_p	0.2 - 1.5 mm
Corner radius	0.2 mm
Number of changes/inserts	2
Cutting speed v_c main application	140 - 400 m/min
Cutting conditions	slightly interrupted
Chip breaker	SS

Data sheet

ISO code indexable insert	VCMT 160402
Main application	P
Type of product	Indexable insert for turning