

Garant**Indexable insert for turning VNMG 160408, for finish machining****Order data**

Order number	251734 HB7010-2
GTIN	4069515018166
Item class	21G

Technical description

Number of changes/inserts	4
Cutting speed v_c main application	170 - 500 m/min
Finishing/roughing assignment	Finishing
Main application	P
Corner radius	0.8 mm
Chip breaker	SS
Type	HB7010-2
ISO code indexable insert	VNMG 160408
Cutting depth a_p	0.3 - 2 mm
Cutting conditions	continuous
Feed f	0.1 - 0.4 mm/rev.

Data sheet

Tool material	Carbide
Type of product	Indexable insert for turning