

Garant**Indexable insert for turning VB.T 110304, for medium machining****Order data**

Order number	261224 HB7010-2
GTIN	4069515022095
Item class	21G

Technical description

Chip breaker	SM
Cutting speed v_c main application	120 - 440 m/min
Corner radius	0.4 mm
Tool material	Carbide
Number of changes/inserts	2
Cutting conditions	continuous
Main application	P
Finishing/roughing assignment	Finishing
Feed f	0.08 - 0.3 mm/rev.
ISO code indexable insert	VBMT 110304
Cutting depth a_p	0.3 - 2 mm

Data sheet

Tolerance	M
Type	HB7010-2
Type of product	Indexable insert for turning