

**Indexable insert for turning TCMT 16T308, for medium machining****Order data**

Order number	260988 HB7035-2
GTIN	4069515021777
Item class	21G

Technical description

Feed f	0.08 - 0.3 mm/rev.
Type	HB7035-2
Cutting depth a_p	0.3 - 2 mm
Finishing/roughing assignment	Finishing
Main application	P
Chip breaker	SM
Number of changes/inserts	3
Corner radius	0.8 mm
Tolerance	M
Cutting speed v_c main application	80 - 290 m/min
Tool material	Carbide
ISO code indexable insert	TCMT 16T308

Data sheet

Cutting conditions

heavily interrupted

Type of product

Indexable insert for turning