

Garant**Indexable insert for turning VB.T 160408, for medium machining****Order data**

Order number	261234 HB7035-2
GTIN	4069515022255
Item class	21G

Technical description

Tolerance	M
Main application	P
Number of changes/inserts	2
Corner radius	0.8 mm
ISO code indexable insert	VBMT 160408
Cutting speed v_c main application	80 - 290 m/min
Feed f	0.08 - 0.3 mm/rev.
Type	HB7035-2
Finishing/roughing assignment	Finishing
Cutting conditions	heavily interrupted
Cutting depth a_p	0.3 - 2 mm

Data sheet

Chip breaker	SM
Tool material	Carbide
Type of product	Indexable insert for turning