

**Indexable insert for turning TNMG 160404, for finish machining****Order data**

Order number	251432 HB7010-2
GTIN	4069515017800
Item class	21G

Technical description

Feed f	0.1 - 0.4 mm/rev.
Finishing/roughing assignment	Finishing
Corner radius	0.4 mm
Cutting speed v_c main application	170 - 500 m/min
Number of changes/inserts	6
ISO code indexable insert	TNMG 160404
Main application	P
Cutting depth a_p	0.3 - 2 mm
Type	HB7010-2
Tool material	Carbide
Chip breaker	SS
Cutting conditions	continuous

Type of product

Indexable insert for turning