

Garant**Indexable insert for turning DNMG 150608, for medium machining****Order data**

Order number	250762 HB7020-2
GTIN	4069515017121
Item class	21G

Technical description

Corner radius	0.8 mm
Cutting speed v_c main application	130 - 370 m/min
Cutting conditions	slightly interrupted
Feed f	0.2 - 0.5 mm/rev.
Tool material	Carbide
Main application	P
Tolerance	M
Number of changes/inserts	4
Type	HB7020-2
Finishing/roughing assignment	Finishing
ISO code indexable insert	DNMG 150608

Data sheet

Chip breaker	SM
Cutting depth a_p	0.3 - 4 mm
Type of product	Indexable insert for turning