

**Indexable insert for turning CNMG 160612, for medium machining****Order data**

Order number	250170 HB7035-2
GTIN	4069515016148
Item class	21G

Technical description

Corner radius	1.2 mm
Cutting depth a_p	0.3 - 4 mm
Tool material	Carbide
Main application	P
Feed f	0.2 - 0.5 mm/rev.
Tolerance	M
Type	HB7035-2
Chip breaker	SM
ISO code indexable insert	CNMG 160612
Cutting conditions	heavily interrupted
Number of changes/inserts	4

Data sheet

Cutting speed v_c main application	120 - 320 m/min
Finishing/roughing assignment	Finishing
Type of product	Indexable insert for turning