


**Indexable insert for turning TNMG 160408, for medium machining****Order data**

Order number	251544 HB7010-2
GTIN	4069515018029
Item class	21G

Technical description

Type	HB7010-2
Feed f	0.2 - 0.5 mm/rev.
Finishing/roughing assignment	Finishing
Number of changes/inserts	6
Tolerance	M
Cutting conditions	continuous
ISO code indexable insert	TNMG 160408
Main application	P
Tool material	Carbide
Corner radius	0.8 mm
Chip breaker	SM
Cutting speed v_c main application	140 - 440 m/min

Data sheet

Cutting depth a_p	0.3 - 4 mm
Type of product	Indexable insert for turning