

Garant**Indexable insert for turning CNMG 160612, for roughing machining****Order data**

Order number	250336 HB7035-2
GTIN	4069515016445
Item class	21G

Technical description

Main application	P
Type	HB7035-2
Cutting speed v_c main application	100 - 290 m/min
Chip breaker	SG
Cutting conditions	heavily interrupted
Finishing/roughing assignment	Roughing
ISO code indexable insert	CNMG 160612
Number of changes/inserts	4
Tool material	Carbide
Cutting depth a_p	1.5 - 6 mm
Corner radius	1.2 mm

Data sheet

Feed f	0.25 - 0.6 mm/rev.
Type of product	Indexable insert for turning