

Garant**Indexable insert for turning DC.T 11T308, for medium machining****Order data**

Order number	260464 HB7010-2
GTIN	4069515020688
Item class	21G

Technical description

Feed f	0.08 - 0.3 mm/rev.
Finishing/roughing assignment	Finishing
Cutting speed v_c main application	120 - 440 m/min
Chip breaker	SM
Cutting depth a_p	0.3 - 2 mm
Corner radius	0.8 mm
Tool material	Carbide
Number of changes/inserts	2
Type	HB7010-2
Tolerance	M
ISO code indexable insert	DCMT 11T308

Data sheet

Cutting conditions	continuous
Main application	P
Type of product	Indexable insert for turning